



Ref. Certif. No.

US-32465-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the factory

XP POWER LLC
990 BENECIA AVE SUNNYVALE CA 94085
USA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

Input: 100 - 240VAC 50/60Hz 2.2A
See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

ECM100UXY
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014 / A11:2017;
National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6021-CB-1 issued on 2018-09-19

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-09-25

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-32465-UL

Model Details:

ECM100UXY

Where X represents D2, T3 or Q4, and Y represents 1 to 7. May be provided with suffix (3X5) or *.

Factories:

XP POWER (S) PTE LTD

LIPO BLDG, #05-01 621 ALJUNIED RD SINGAPORE 389834
SINGAPORE

XP POWER (KUNSHAN) LTD

230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215300
CHINA

XP POWER (VIETNAM) CO LTD

LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG BINH DUONG
VIETNAM

XP POWER PLC

16 HORESHOE PARK PANGBOURNE RG8 7JW
UNITED KINGDOM

Ratings:

Output:

V1: 5.0 or 3.0 Vdc, 12.0 or 10.0 A

V2: 3.3, 5.0, 12.0, 15.0 or 24.0 Vdc, 2.0, 3.0 or 5.0 A

V3 (optional): -5.0, +/-12.0 or +/-15.0 Vdc, 0.8 A

V4 (optional): -5.0, -12.0 or -15.0 Vdc, 0.5 A

Maximum 100 W combined outputs.

See enclosure 'Miscellaneous' for specific output ratings.

Additional information (if necessary)



UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-09-25

Signature:

Jolanta M. Wroblewska