


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	AC-DC Power Supply
Name and address of the applicant	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	XP POWER (KUNSHAN) LTD 230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215300 CHINA <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	AHM85PSXXYY-ZW##V See Page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 62368-1:2014/A11:2017. National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E139109-A6015-CB-1 issued on 2018-08-31

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Ppingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2018-09-03

Signature:

For full legal entity names see www.ul.com/ncbnames

Jolanta M. Wroblewska



Ref. Certif. No.

US-32387-UL

Model Details:

AHM85PSXXYY-ZW##V Where XX is any number between 12-24, YY can be blank or C2, Z can be blank or A, W can be blank, 6, or 8, # can be blank or any alphanumeric character, and V can be blank or any alphanumeric character, may be provided with or without "-".

Factories:

XP POWER LLC
990 BENEZIA AVE SUNNYVALE CA 94085
UNITED STATES

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG BINH DUONG
VIETNAM

Ratings:

Input:

100 - 240V ac 1.0A, 50/60Hz

Output at 40°C (100% load):

Model AHM85PS12: 12 Vdc (10.1-13.5 Vdc), 7.08 A max. (85W max)

Model AHM85PS15: 15 Vdc (13.6-17.0 Vdc), 5.67 A max. (85W max)

Model AHM85PS19: 19 Vdc (17.1-21.0 Vdc), 4.47 A max. (85W max)

Model AHM85PS24: 24 Vdc (21.1-26.0 Vdc), 3.54 A max. (85W max)

Output voltage rating indicated in parenthesis represents voltage tolerance evaluated.

All outputs are de-rated to 60% load at 60°C.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-09-03

Signature:

Jolanta M. Wroblewska