


10W

The JMR10 series is a range of ultra-compact, regulated PCB-mount medical DC-DC converters which offers single and dual output voltages ranging from 5V to 15V. Housed in a ultra-compact DIP24 package, the JMR10 series features a 4:1 input voltage range and offers a ±10% output trim on single output versions. Its low no load power increases efficiency and extends runtime in battery powered applications. The JMR10 series features worldwide medical approvals, 2 x MOPP 5kVAC reinforced isolation and extremely low leakage currents benefitting system designers with easy integration into a wide range of BF and CF rated medical applications including imaging, patient monitoring, surgical equipment, patient treatment and dentistry.

Features

- Regulated single & dual outputs from 5 to 30VDC
- 4:1 input range
- Ultra-compact DIP24 PCB mount package
- Low no-load power
- 10% trim on single output versions
- IEC60601-1 medical safety agency approvals
- 5kVAC reinforced isolation
- 2 x MOPP at 250VAC
- 2µA patient leakage current
- Remote On/Off
- Short circuit, overload & overvoltage protection
- •-40°C to +100°C operating temperature
- 3 year warranty

Models & Ratings



Notes:

- 1. Dual output models can be used to provide a single output of 10V, 24V or 30V.
- 2. Specifications noted using nominal input voltage and full load at 25°C unless otherwise stated.

DC-DC CONVERTER



Dimensions

31.8 x 20.3 x 10.2mm (1.25" x 0.8" x 0.4")

Applications









Healthcare

Healthcare

Electronics

Medical Diagnostics

More Resources

Click the link or scan the code





- 3. Measured at full load and nominal input voltage.
- 4. No load input current reduces to <3mA when module is inhibited.
- 5. Available for OEM quantities, please contact sales.

Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
	4.5		18		12V nominal
Input Voltage Range	9		36	VDC	24V nominal
	18		75		48V nominal
Inrush Current			80	Α	At nominal input voltage
Input Reflected Ripple		20		mA pk-pk	Through 12μH inductor and 47μF capacitor
			25	VDC for 100ms	12V nominal
Input Surge			50		24V nominal
			100	101 1001113	48V nominal
Input Current Remote On/Off		2.5	8.0	mA	Idle current using remote "Off". See models and ratings table for no load input current with module "On"
		5.0		А	12V nominal
Recommended Input Fuse (Slow blow)		2.0			24V nominal
(Slow blow)		1.0			48V nominal

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Output Voltage	5		30	VDC	See Models & Ratings table	
Output Voltage Adjustment	-10		+10	%	See application note	
Initial Set Accuracy			±1	%	At full load	
Minimum Load	0			%	No minimum load required	
Line Regulation			±0.5	%	From min to max input voltage	
Load Regulation			±1.0	%	From 0-100% load	
Cross Regulation			±5	%	Dual output, when one output at 25% load other is varied from 10% to full load	
Transient Response Deviation	3		5	%	Deviation recovering to within 1% in 250µs for 25% load change at 0.1A/µs	
Ripple & Noise			75/100	mV pk-pk	5V/12-15V outputs, 20MHz bandwidth, measured using 10µF cerami capacitor at nominal Vin	
Short Circuit Protection	Continuous, I	niccup mode	with auto recover	y		
Maximum Capacitive Load	See Models 8	& Ratings tal	ole			
Temperature Coefficient			0.02	%/°C		
Overload Protection		160		%	At nominal input voltage	
Remote On/Off	Output is on if remote on/off (pin 1) is open with reference to pin 2 -Vin Output turns off if 2.2 to 12V is applied to remote On/Off (pin 1) or if connected to a current source of 2-4mA. See application note					

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Efficiency		87		%	See Models & Ratings table	
Isolation: Input to Output	5000			VAC	Reinforced insulation, 2 x MOPP, 60s, production test to 5kVAC	
Working Voltage			250	VAC		
Creepage and Clearance	8			mm		
Isolation Resistance	10 ⁹			Ω	Input to output	
Isolation Capacitance		17		pF	Input to output	
Leakage Current		2		μΑ	264VAC, 60Hz	
Power Density			1.5	Wcm ³		
Mean Time Between Failure	650			khrs	MIL-HDBK-217F, +25°C GB	
Switching Frequency		300		kHz		
Weight		14.0 (0.003)		g (lb)		
Solder Profile			260	°C	Waveflow. 1.5mm (0.05") from case, 10 seconds max.	
Case Material	Non conductive black plastic UL94V-0 rated					
Potting Material	Silicone, UL94V-0 rated					
Pin Material	Solder coated brass dia. 0.5mm					
Water Wash	Use deionized water. Dry thoroughly					



Environmental

Characteristic	Minimum	Typical	Maximum	aximum Units Notes & Conditions	
Operating Temperature	-40		+100	°C	See derating curve
Storage Temperature	-55		+125	°C	
Case Temperature			+110	°C	At nominal input voltage
Humidity Operating & Storage	5		95	%RH	Non-condensing
Cooling	Natural conv	ection			
Operating Altitude			5000	m	Transport altitude 10km

Safety Approvals

Safety Agency	Standard	Notes & Conditions
UL	ANSI/AAMI ES60601-1, UL62368-1	
CSA	CSA C22.2 No. 60601-1	
TUV	EN60601-1	
СВ	IEC/EN60601-1	
CE	Meets all applicable directives	
UKCA	Meets all applicable legislation	

EMC: Emissions


Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55011	Class B	See application notes
Radiated	EN55011	Class B	


EMC: Immunity


Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Medical Device EMC	EN60601-1-2: 2015			IEC60601-1-2:2014 Ed4.0
ESD Immunity	EN61000-4-2	±8kV	^	Contact
	EIN61000-4-2	±15kV	A	Air
Radiated Immunity	EN61000-4-3	10V/m	Α	
EFT/Burst	EN61000-4-4	±2kV	Α	External component required, see application notes
Surge	EN61000-4-5	±2kV	Α	External component required, see application notes
Conducted Immunity	EN61000-4-6	10Vrms	Α	
Magnetic Fields	EN61000-4-8	100A/m	Α	



Mechanical Details








Fill Collifections							
Pin	Single	Dual					
1	CTRL	CTRL					
2	-Vin	-Vin					
10	Trim	Trim					
11	NC	-Vout					
14	+Vout	+Vout					
16	-Vout	COM					
22	+Vin	+Vin					
23	+Vin	+Vin					

Recommended PCB Footprint



There should be at least 8mm distance between primary and secondary circuit.

Through hole diameter 0.8mm (0.031")
Pad diameter top side 1.0mm (0.039")
Pad diameter bottom side 2.0mm (0.079")

Notes:

- 1. All dimensions are in mm (inches)
- 2. Weight: 14.0 (0.03) g (lbs) approx.
- 3. Pin diameter: ±0.002, 0.02 (±0.05, 0.5)


- 4. Pin pitch tolerance: ±0.35 (±0.014)
- 5. Case tolerance: ±0.5 (±0.02)

Application Notes

EMC Filter

Circuit 1 for Surge & EFT, 2 for EMI class B.


Single Output



Model Number	D1	C1 ⁽¹⁾	C2, C3	L1	L2
JMR1012XXX	SMDJ26A	470µF/100V	MLCC, 22µF, 35V	2.2µH	LFD648074-52UH-3.14A
JMR1024XXX	SMDJ58A	330µF/100V	MLCC, 4.7μF, 50V	4.7μH	LFD649075-175UA-1.76A
JMR1048XXX	SMDJ120A	330µF/100V	MLCC, 2.2μF, 100V	6.8µH	LFD649075-419UH-0.78A

⁽¹⁾ Nippon CHEMI-CON KY series

Remote On/Off




Module "On" if pin 1 is open circuit Module "Off" if pin 1 is connected to current source of 2-4mA, or a voltage of 2.2 to 12V is applied to pin 1 WRT pin 2.


Application Notes

Derating Curves

JMR1012S05, JMR1012D05, JMR1024S05, JMR1024D05




JMR1012S12, JMR1012D12, JMR12S15, JMR12D15



Ambient Temperature (°C)

JMR1048S05, JMR1048D05



JMR1024S12, JMR1024S15, JMR1024D12, JMR1024D15, JMR1048S12, JMR1048S15, JMR1048D12, JMR1048D15

