

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Component Switching Power Supply

Name and address of the applicant

XP POWER L L C
15641 Red Hill Avenue, Suite 100
Tustin, CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 Red Hill Avenue, Suite 100
Tustin, CA 92780 USA

Name and address of the factory

Note: When more than one factory, please report on page 2

XP Power LLC
990 Benecia Ave Sunnyvale, CA 94085
USA Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

ECM100USXX, ECM100USXX*, ECM100US12,
ECM100US33>2413, ECM100US12>2516,
ECM100US12>2662, ECM100USXX 3X5, See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 60601-1:2006/ A1:2013/
A12:2014; National Differences specified in the CB Test Report. Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005

As shown in the Test Report Ref. No. which forms part of this Certificate

E146893-D1039-1/A0/C0-ULCB issued on 2019-07-23

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-07-30

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-34108-UL

Model Details:

ECM100USXX, ECM100USXX*, ECM100US12, ECM100US33>2413, ECM100US12>2516, ECM100US12>2662 and ECM100USXX 3X5, where XX can be any number between 03 and 48 designating the output voltage; Additionally all model(s) may have suffix -C or -W or -both.

Factories:

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RDZHANGPU TOWN, KUNSHANJIANGSU 215300
CHINA

Ratings:

All Models (Except Models ECM100US12-C, ECM100US12>2516 and ECM100US12>2662):

Input: 100-240 V~, 50/60 Hz, 2.2 A

Output: See Model Differences section in Test Report for details

Models ECM100US12>2516 and ECM100US12>2662:

Input: 100-240 V~, 50-60 Hz, 2.2 A

Output: See Model Differences section in Test Report for details

Model ECM100US12 / ECM100US12-C:

Input: 100-240 V~, 50-60 Hz, 1.0 A

Output: 12 Vdc, 3.75 A, 45 W

Model ECM100US33 / ECM100US33-C:

Input: 100-240 V~, 50/60 Hz, 1.4 A

Output: 33 Vdc, 1.97 A, 65 W

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-07-30

Signature:

Jolanta M. Wroblewska