



Ref. Certif. No.

US-32789-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the factory

8-1 FU KUNG RD FU HSING PARK FU HSING HSIANG
CHANGHUA HSIEN 506
TAIWAN

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

ECL15US24-XD0030B, ECL15USXX-Y-ZZ
See Page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications.
 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E317867-A6024-CB-1 issued on 2019-04-18

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-04-23
Original Issue Date: 2018-11-21

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-32789-M1-UL

Model Details:

ECL15US24-XD0030B, ECL15USXX-Y-ZZ

Where "XX" is 03, 05, 09, 12, 15, 24 or 48, "Y" is E, P, T or S, "Z" is any alphanumeric character or blank. "-" is optionally provided.

Factories:

1 JING XIANG RD DONGCHENG FOREIGN TRADE INDUSTRIAL PARK ZHUSHAN DONGCHENG DISTRICT
DONGGUAN GUANGDONG 523128
CHINA

Ratings:

Input:

ECL15USXX-Y-ZZ:

100-240V~ 0.6A 50-60Hz

ECL15US24-Y-ZZ and ECL15US24-XD0030B:

100-240V~ 0.6A 50-60Hz or 100-350Vdc 0.2A

Output:

ECL15US03-Y: 3.3Vdc 3A

ECL15US05-Y: 5Vdc 3A

ECL15US09-Y: 9Vdc 1.67A

ECL15US12-Y: 12Vdc 1.25A

ECL15US15-Y: 15Vdc 1A

ECL15US24-Y-ZZ and ECL15US24-XD0030B: 24Vdc 0.63A

ECL15US48-Y: 48Vdc 0.32A

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

Amendment 1 (Technical):

- Model Differences section updated for clarity.
- Energy Source Table and Safeguards Table: MS evaluation removed.
- Updated Clauses 5.4.4, F3.5.3, F3.6, G.8
- Updated Tables 5.2, 5.4.9, B.2.5, B.4

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbnames

Date: 2019-04-23

Original Issue Date: 2018-11-21

Signature:

Jolanta M. Wroblewska