



Ref. Certif. No.

DK-148221-A1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Medical DC-DC converter
Name and address of the applicant	XP POWER LTD 19 Tai Seng Avenue #07-01 Singapore 534054 Singapore
Name and address of the manufacturer	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the factory	No.66 Yuanying Rd., Liaobu Town, Dongguan City, Guangdong 523412, P.R. China
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	Input: 9-18 Vdc, 4A 18-36 dc, 2A 36-75Vdc, 1A <input checked="" type="checkbox"/> Additional Information on page 2
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	JHM30xxS05, JHM30xxS12, JHM30xxS15, JHM30xxD05, JHM30xxD12, JHM30xxD15 <input checked="" type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to: EN 60601-1:2006, EN 60601-1:2006/A1:2013, EN 60601-1:2006/A12:2014, EN 60601-1:2006/A2:2021 The report was revised to include administrative modifications. The risk management requirements of the standard were not addressed National Differences: EU Group Differences, CA, JP, GB, US <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60601-1:2005, IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005/AMD2:2020
As shown in the Test Report Ref. No. which forms part of this Certificate	NC34388-D6001-CB-1 issued on 2023-12-27

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2023-12-27
Original Issue Date: 2023-12-12

Signature:
Thomas Wilson



Ref. Certif. No.

DK-148221-A1-UL

Factory(ies):

8-1, Fu Kung Rd., Fu Hsing Park., 506 Fu Hsing Hsiang, ChangHua Hsien., Taiwan

Additional Model Detail(s):

JHM30xxS05, JHM30xxS12, JHM30xxS15, JHM30xxD05, JHM30xxD12, JHM30xxD15, where xx = input DC voltage (12, 24 or 48)

Additional Ratings:

Output: See CB test report for additional details.

Summary of Modifications:

Update National Differences information. See CB test report for additional details.

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2023-12-27

Original Issue Date: 2023-12-12

Signature:

Thomas Wilson