



Product Service

# CERTIFICATE

No. B 057396 0474 Rev. 01

**Holder of Certificate:** **XP Power LLC.**  
15641 Red Hill Avenue, Suite 100  
Tustin CA 92780  
USA

**Certification Mark:**



**Product:** **Switching power supply unit**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

**Test report no.:** 095-72143924Q-000

**Valid until:** 2024-06-23

**Date,** 2019-06-28

( Adrian Rabago Valenzuela )



Product Service

# CERTIFICATE

No. B 057396 0474 Rev. 01

### Model(s):

**ECE40USxx**

(where xx can be number between 03 to 48 designating the output voltage, may also be provided with suffix "S" and/or "D", "-" provided optionally)

### Brand Name:

**XP**



### Parameters:

Rated Input Voltage: 100-240 VAC

Rated Frequency: 50-60 Hz

Rated Input Current: 1.2 A

Protection Class: Class I or Class II at end use

Maximum Temperature, Ambient: 50°C at 100% rated output  
70°C at 50% rated output

Elevation for use: 0-3048 m

### Approved models and Rated Outputs:

Model Number	OUTPUT RATING	
	Voltage (VDC )	Current (A)
ECE40US03	3.3	10
ECE40US05	5	8
ECE40US09	9	4.44
ECE40US12	12	3.33
ECE40US15	15	2.67
ECE40US24	24	1.67
ECE40US48	48	0.83

Additional Suffix "S" denotes units provided with Screw Terminals.  
Additional Suffix "D" denotes units provided with DIN Rail mounting Clip.

ZERTIFIKAT • CERTIFICATE • 認證證書 • CERTIFICADO • CERTIFICAT



Product Service

# CERTIFICATE

No. B 057396 0474 Rev. 01

### Conditions of Acceptability:

When installing the equipment, all requirements of the standards and the manufacturer's specifications must be met.

### The models require:

- A suitable electrical and fire enclosure must be provided in the end use equipment.
- The product is intended for use on the following power systems: TN.
- The following output circuits are at ES1 energy levels: All.
- The following output circuits are at PS3 energy levels: All.
- Sufficient clearance and creepage distance shall be provided between the primary circuit and accessible conductive parts at end product.
- The following input terminals/connectors must be connected to the end-product supply neutral: ACN.
- A suitable main disconnect device shall be provided in the end product.
- Proper bonding to the end-product main protective earthing terminal is required when installed in Class I end product, ground bond test shall be conducted.
- Touch current test and dielectric Strength test need to be considered at end use equipment.

**Tested according to:** EN 62368-1:2014/A11:2017

**Production Facility(ies):** 061661, 077041

ZERTIFIKAT ♦ CERTIFICATE ♦ 認 證 證 書 ♦ CERTIFICADO ♦ CERTIFICAT