



Product Service

CERTIFICATE

No. Z1A 124843 0002 Rev. 00

Holder of Certificate: **XP Power LLC.**
15641 Red Hill Avenue, Suite 100
Tustin CA 92780
USA

Certification Mark:



Product: **Adaptors
(AC ADAPTOR)**

Tested according to: EN IEC 62368-1:2020/A11:2020
EK1 557-13
AfPS GS 2019:01 PAK

With this certificate, in its capacity as a notified GS body, TÜV SÜD Product Service GmbH issues the GS Mark to the named certificate holder for the declared product with the named model designation in accordance with section 20 ProdSG (German Product Safety Act). The product meets the safety and health requirements of section 20 (3) ProdSG. The manufacturer is reminded of their obligations in accordance with section 24 ProdSG. The certification marks shown above can be affixed on the product. It is not permitted to alter the certification marks in any way. In addition, the certificate holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 64210230074801A

Valid until: 2028-04-24

Date, 2024-04-02

(Richard Zhu)

CERTIFICATE

No. Z1A 124843 0002 Rev. 00

Model(s):

**VFL05USwww-yy-zz, VFR05USwww-zz,
VER05US050-zz**
(www=040-120 stands for rated output voltage range 4.0-12.0VDC in step of 0.1V; yy=EU, UK stands for different AC plug type: EU for European plug, UK for United Kingdom Plug; zz=JA, UB, MB, CB, BB stands for different output port type: JA stand for DC connector with output cord, UB or MB or CB stands for USB port with output cord for 5VDC only, BB stand for output with USB socket for 5VDC only.)

Brand Name:

XP



Parameters:

Rated Input: 100-240VAC, 50/60Hz, 0.18A

Rated Output: See below table for details

Protection Class: II

Degree of Protection: IP20

Remark: Product name 'SWITCHING POWER SUPPLY'

Model	Rated output voltage (VDC)	Rated output current (A)	Max. output power (W)
VFL05USwww-yy-zz, VFR05USwww-zz	4.0-7.9	0.01-1.2	6.0
	8.0-12.0	0.01-0.75	6.0
VER05US050-zz	5.0	0.01-1.0	5.0